

## SERIES 60

### INJECTION POLYURETHANE WHEELS WITH POLYAMIDE 6 CENTRE



#### Wheel description

Injection polyurethane tread, hardness 55 Shore D. Polyamide 6 centre.

#### Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing, with ball bearing, with stainless steel ball bearing.

**Diameters:** 80-250 mm

**Carrying capacities:** 120-750 daN

### Fittings with swivel, fixed and swivel with brake brackets



#### Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm  
Models available: with top plate fastening, with bolt hole  
Suitable brakes: front-locking and central (hexagonal) brake systems



#### Medium duty brackets type M

Max. carrying capacity 500 daN – available diameters 160-200 mm  
Top plate fastening.  
Adjustable front-locking brake



#### Medium-heavy duty brackets type P

Max. carrying capacity 750 daN – available diameters 100-200 mm  
Top plate fastening.  
Front-locking and adjustable rear-locking brake systems

### Uses

#### Environments

Suitable for environment with atmospheric agents, alcohol and glycol; not suitable for applications where mineral and organic acids, base solutions and saturated vapour are present.

Usage temperatures: from -15 °C to +70 °C

#### Floors



#### Handling

