

## SERIES 67

### SOLID THERMOSETTING RESIN WHEELS



#### Wheel description

Solid high temperature thermosetting resin wheels.

#### Hub

The plain bearing bore results from a hole in the material forming the centre of the wheel and contains the axle.

**Diameters: 80-200 mm**

**Carrying capacity: 150-500 daN**

### Fittings with swivel, fixed and swivel with brake brackets



#### Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems



#### Medium-heavy duty brackets type P - PX

Max. carrying capacity 750 daN – available diameters 80-200 mm

Models available: with top plate fastening

Suitable brakes: front-locking and adjustable rear-locking brake systems

### Uses

#### Environments

Suitable for applications in humid environments, where medium-harsh chemicals are present.

The series is used mainly for motionless applications, especially in high temperatures environments.

Typical usage: ovens, especially in bakery and ceramics sectors.

Usage temperatures: from -20°C to +300°C

#### Floors



#### Handling

